



**MITSUBISHI
ELECTRIC**

MULTIMEDIA DATA/VIDEO PROJECTORS

Changes for the Better



Entry level, with high specs.



Mobile XGA

XD211U



New DLP® chip, 2200lm of brightness and weighs less than 6.0 lbs

The XD211U combines the features of an advanced DLP® (Digital Light Processing) chip, a newly developed optical engine and a high-efficiency 180W light source lamp to produce an incredible picture with rich and vibrant colors. Additionally with its compact and lightweight design, the new XD211U allows you easy portability and quick setups for those presentations on the go.

Detachable Keypad

The keypad* can be removed from the projector to be used as a remote control. Since the keypad is used to control the projector, detaching it also doubles as a key-lock function preventing others from making adjustments and helps discourage theft.

* An extra remote keypad is included with the XD211U should the original keypad get lost.



Anti-theft Security Hook

An anti-theft security hook* is built into the projector to help prevent theft and any unauthorized removal of the projector.

* Mitsubishi Electric cannot accept responsibility for thefts occurring despite use of this safety feature.

Instant Shutdown

Once your presentation is over, you can simply hit the power button, disconnect the XD211U and go off to your next task. Engineered with the instant shutdown feature there is no longer any awkward idle time waiting for the projector to completely power off. Now there is no longer any shut down delays and now your projector can keep up with your busy presentation schedule.

Easy Setup

Auto Search function displays the connected input sources automatically. Users don't have to get distracted by ensuring the appropriate source is manually selected. Also, +/-20 degrees of vertical keystone correction and 1.2x optical zoom gives users a greater flexibility of positioning.

White Intensity

Users have the flexibility to adjust the light intensity of the whiteness of the color wheel of up to 11 levels. Allowing users to configure the overall brightness and picture parameters tailored to their individual preference.

- Optimum high-contrast picture quality, to brighten up PC images.

White enhancement 0			White enhancement 5			White enhancement 11		
100%	100%	100%	100%	100%	100%	100%	100%	100%
100%	100%	100%	100%	100%	100%	100%	100%	100%
100%	100%	100%	100%	100%	100%	100%	100%	100%
100%	100%	100%	100%	100%	100%	100%	100%	100%

White enhancement 0 White enhancement 5 White enhancement 11

Superior Color Reproduction


The XD211U is equipped with a 5 segmented color wheel (R,G,B,W,Y), BrilliantColor™ technology and a newly designed dynamic lamp power control system to produce superior and more natural color reproduction.



XD211U


MOBILE XGA PROJECTOR

Input and Output Terminals



- 1 Audio output
- 2 S-Video
- 3 PC/Component Video output
- 4 Serial RS-232C
- 5 PC/Component Video input (mini D-sub 15pin)
- 6 RCA
- 7 Audio input (stereo mini jack)

Dimensions




Specifications

Model	XD211U
Display Technology	0.55" 1-Chip DMD
Resolution	1024 x 768 (Total 786,432 pixels)
Brightness	2200lm
Contrast Ratio	2000 : 1
Picture Size	40" - 300"
Source Lamp	150W (life up to 3000hrs) with Low Mode, 180W (life up to 2000hrs) with Standard Mode
PC Compatibility	640 x 480 - 1280 x 1024, True : 1024 x 768, Sync on Green available
Video Compatibility	NTSC / NTSC 4.43 / PAL (including PAL - M , N) / SECAM / PAL - 60 Component Video ; 480i/p (525i/p), 576i/p (625i/p), 720p (750p), 1080i (1125i 60Hz), 1080i (1125i 50Hz)
PC Input Terminals	RGB ; mini D-sub 15pin x 1 Audio ; Stereo mini jack (ø3.5mm) x 1
Video Input Terminals	RCA x 1 + S-VIDEO x 1
Output Terminals	RGB ; mini D-sub 15pin x 1 Audio ; Stereo mini jack (ø3.5mm) x 1
Communication Terminal	RS-232C x 1
Audio Speaker	2W Mono
Dimension (W x H x D)	302 x 105 x 221 mm / 11.9 x 4.1 x 8.7 inch
Weight	2.7kg / 6.0lbs
Power requirements	AC 100 - 240V, 50 / 60Hz
Optional Lamp	VLT-XD210LP

*All brand names and product names are trademarks, registered trademarks or trade names of their respective holders.

Screen size and Projection distance

As seen from the side



Screen size chart (4:3 aspect ratio)

Diagonal size		Screen				Distance from screen (L)				Height projected image (Hd)	
		Width (W)		Height (H)		Max. Zoom		Min. Zoom			
inch	cm	inch	cm	inch	cm	inch	m	inch	m	inch	cm
40	102	32	81	24	61	55	1.4	68	1.7	1.8	5
60	152	48	122	36	91	84	2.1	103	2.6	2.7	7
80	203	64	163	48	122	112	2.8	137	3.5	3.6	9
100	254	80	203	60	152	141	3.6	172	4.4	4.5	11
150	381	120	305	90	229	212	5.4	259	6.6	6.8	17
200	508	160	406	120	305	283	7.2	345	8.8	9.0	23
250	635	200	508	150	381	354	9.0	432	11.0	11.3	29
300	762	240	610	180	457	425	10.8	-	-	13.5	34

The above numbers are approximate, and may be slightly different from the actual measurements.

Screen size chart (16:9 aspect ratio)

Diagonal size		Screen				Distance from screen (L)				Height projected image (Hd)	
		Width (W)		Height (H)		Max. Zoom		Min. Zoom			
inch	cm	inch	cm	inch	cm	inch	m	inch	m	inch	cm
40	102	35	89	20	50	60	1.5	74	1.9	5.2	13
60	152	52	133	29	75	91	2.3	112	2.8	7.9	20
80	203	70	177	39	100	122	3.1	149	3.8	10.5	27
100	254	87	221	49	125	153	3.9	187	4.8	13.1	33
150	381	131	332	74	187	231	5.9	282	7.2	19.6	50
200	508	174	443	98	249	308	7.8	376	9.6	26.2	66
250	635	218	553	123	311	386	9.8	471	12.0	32.7	83
300	762	261	664	147	374	463	11.8	-	-	39.3	100

The above numbers are approximate, and may be slightly different from the actual measurements.

MITSUBISHI ELECTRIC CORPORATION
 HEAD OFFICE : TOKYO BLDG., 2-7-3, MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN

To find out more about XD211U and our projectors, visit us at

Global.MitsubishiElectric.com/projectors/